


**Order form for Flextight Original holders.**

Company name: \_\_\_\_\_

Your reference no.: \_\_\_\_\_

**Flextight Original Holder item no.:**

\_\_\_\_\_ pcs. - \_\_\_\_\_ pcs.  
 \_\_\_\_\_ pcs. - \_\_\_\_\_ pcs.  
 \_\_\_\_\_ pcs. - \_\_\_\_\_ pcs.  
 \_\_\_\_\_ pcs. - \_\_\_\_\_ pcs.



**Description of the Custom Sized Holder:**

**Flextight Photo and 343 only**

Aperture Width (y) (max. width 60 mm)  Quantity of holders:

x  + (n - 1) x 8 mm =   
 No. of apertures,(n) Individual aperture height (x) (in mm) Spacing between apertures (No. of apertures - one x 8 mm) Resulting length (max. length 180 mm)

**Flextight Precision, 646, 848 and 949 only**

Aperture Width (y) (Recommended max. 94 mm)  Quantity of holders:

x  + (n - 1) x 8 mm =   
 No. of apertures,(n) Individual aperture height (x) (in mm) Spacing between apertures (No. of apertures - one x 8 mm) Resulting length (max. length 245 mm)

**Flextight 2848 and Progression only**

Aperture Width (y) (max. width 94 mm)  Quantity of holders:

x  + (n - 1) x 8 mm =   
 No. of apertures,(n) Individual aperture height (x) (in mm) Spacing between apertures (No. of apertures - one x 8 mm) Resulting length (max. length 190 mm)

**Important!** To ensure sufficient hold on the original, you must define the size of the aperture to be at least 2 mm less than the original, in length and width.  
 All apertures **must** have the same size and orientation.

To be filled in by Imacon:  
 Order no.: \_\_\_\_\_  
 Drawing no.: \_\_\_\_\_

# Guide and order form for Flextight Original Holders



**Imacon**

Imacon A/S  
 Hejrevej 30  
 DK-2400 Copenhagen NV  
 Denmark  
 Tel: +45 70 26 08 00  
 Fax: +45 70 26 09 00


Imacon Inc.  
 15207 N.E. 95th Street  
 Redmond, WA 98052-2562  
 Tel: (425) 861-6434  
 Fax: (425) 861-8838  
 Toll Free: (800) 367-6434

Imacon Germany  
 An der Strusbek 8d  
 22926 Ahrensburg  
 Tel: +49 4102 6674-10  
 Fax: +49 4102 6674-19

www.imacon.dk


**Standard Flextight Original Holders for Flextight 646, 848 and 949**

24x36 (24x35mm)  
(0,94"x1,38")



Item no.50200401

4"x5" (94x119mm)  
(3,70"x4,69")




Item no.50200402

6x7 (57x70mm)  
(2 1/4"x2,76")



Item no.50200403


6x6 (57x57mm)  
(2 1/4"x2 1/4")



Item no.50200404


**Standard Flextight Original Holders for Flextight 343**

24x36 (24x35mm)  
(0,94"x1,38")




Item no.50200419

6x7/6x4,5 (57x70/57x45mm)  
(2 1/4"x2,76"/2 1/4"x1,77")



Item no.50200420


6x6 (57x57mm)  
(2 1/4"x2 1/4")



Item no.50200421


**Flextight Original Holders for Photo and Flextight 343 Please fill in the order form**

6x12 (57x120mm)  
(2 1/4"x4,72")




Item no.50200422

6x18 (57x180mm)  
(2 1/4"x7,17")




Item no.50200423

24x36x4 (24x149mm)  
(0,94"x5,87")




Item no.50200424

6x9 (57x90mm)  
(2 1/4"x3,54")




Item no.50200425

57x88mm  
(2 1/4"x3,46")



Item no.50200426

6x8 (57x78mm)  
(2 1/4"x3,07")



Item no.50200427


**Flextight Original Holders for Precision, Progression, 646, 848, 949 and 2848. Please fill in the order form**

6x9 (57x90mm)  
(2 1/4"x3,54")




Item no. 50200405

6x8 (57x78mm)  
(2 1/4"x3,07")




Item no. 50200406

4,5x6 (45x57mm)  
(1,77"x2 1/4")




Item no. 50200407

9x12 (83x113mm)  
(3,27"x4,45")



Item no. 50200408


13x18 (120x172mm)  
(4,72"x6,77")



Item no. 50200409


Full width is not supported  
by Flextight 949

24x36x5 (24x35mm)  
(0,94"x1,38")




Item no. 50200410

24x36x4 (24x149mm)  
(0,94"x5,87")




Item no. 50200411

6x17 (57x171mm)  
(2 1/4"x6,73")




Item no. 50200412

6x12 (57x120mm)  
(2 1/4"x4,72")




Item no. 50200413

Reflex 4"x6" (94x147mm)  
(3,7"x5,79")




Item no. 50200414  
Not for Progression  
and 2848

60x60x3 (57x182mm)  
(2 1/4"x7,17")




Item no. 50200415

24x36x6 (24x226mm)  
(0,94"x8,9")




Item no. 50200416  
Not for Progression and 2848

24x65mm  
(0,94"x2,56")




Item no. 50200417

57x88mm  
2 1/4"x3,46"




Item no. 50200418

35mm Slide  
mount holder  
only for FT 848



Item no. 50200100

35mm Slide Adaptor Kit  
only for Precision



Item no. 50200050

For custom made Flextight Original Holders please see the reverse side